Aeras® by Ramvac® knows before you do.



Your utility room is the heart of your practice. It has to work. It should never disrupt or distract you from improving the lives of your patients.



Every Aeras compressor or vacuum comes standard with smart monitoring.

Built to Perform Under Pressure

DRY, CLEAN AIR:

Dry air from compressor prevents bacteria growth and air is filtered to 0.01 microns, trapping most airborne bacteria and microbes.

QUIET AS A CONVERSATION:

The new integrated compressor Sound Shield provides sound level that is quiet as a conversation.

DEPENDABLE AND LONG-LASTING:

Because Ramvac vacuums are lubricated, they far outlast non-lubricated systems, and the unique rocking-piston design of the compressor doubles the life of the compression rings compared to a standard piston design.





GENERAL COMPRESSOR INFORMATION

Item No.	Voltage	Dimensions W x D x H (in)	No. of Users	Breaker Size		
C3-12	115v / 230v	30" x 21" x 26"	3	15 amp		
C3-12SS	115v / 230v	30" x 20" x 26"	3	15 amp		
C4-12	115v / 230v	30" x 21" x 26"	4	20 amp		
C4-12SS	115v / 230v	30" x 20" x 26"	4	20 amp		
C6-2	230v	35" x 25" x 30"	6	20 amp		
C7-2	230v	35" x 25" x 30"	7	30 amp		
C11-2	230v	41" × 29" × 32"	11	40 amp		

GENERAL VACUUM INFORMATION

Item No.	Input Power	Stacked Dimensions (Pump and Tank)	No. of Users	Breaker Size
RV4-12T	115v or 230v, 1 ph 60 Hz	29" × 19" × 48"	4	15 amp
RV5-2T	230v, 1 ph 60 Hz	33" x 21" x 59"	5	20 amp
RV7-2T	230v, 1 ph 60 Hz	33" x 21" x 59"	7	20 amp
RV10-2T	230v, 1 ph 60 Hz	33" x 22" x 59"	10	20 amp



©2022 DENTALEZ, Inc. Aeras and DENTALEZ are registered trademarks of DENTALEZ, Inc. Ramvac is a registered trademark of Ramvac Dental Products, Inc.